

Preferred by the pros.



Leading supplier of innovative plumbing products for wholesalers, contractors and specialty builders.



# **CLICK-FIT BATH WASTE** Easy to Install: Save money.

# HALF KITS

- Patent-pending lock-in-place faceplate prevents loosening of overflow and retainer nut which could lead to serious overflow problems
- Unique overflow test cap prevents installation of faceplate without removal of testing device which could cause water damage
- Click-Fit trim is compatible with most major manufactures kits
- Click-Fit re-fit kits available for quick and easy trim outs in special finish
- Assembled in the USA with domestic and foreign components



### **PUSH & SEAL HALF KIT**

PART NO.	DESCRIPTION	
MLCFWH300BX-BN	PVC Push & Seal Half Kit Brushed Nickel	
MLCFWH300BX-CAFÉ	PVC Push & Seal Half Kit Café	
MLCFWH300BX-ORB	PVC Push & Seal Half Kit Oil Rubbed Bronze	
MLCFWH300-CP	PVC Push & Seal Half Kit Chrome	
MLCFBH300BX-BN	ABS Push & Seal Half Kit Brushed Nickel	
MLCFBH300BX-CAFÉ	ABS Push & Seal Half Kit Café	
MLCFBH300BX-ORB	ABS Push & Seal Half Kit Oil Rubbed Bronze	
MLCFBH300-CP	ABS Push & Seal Half Kit Chrome	



### LIFT & TURN HALF KIT

PART NO.	DESCRIPTION
MLCFWH100BX-BLM	PVC Lift & Turn Half Kit Black Matte
MLCFWH100BX-BB	PVC Lift & Turn Half Kit Brushed Bronze
MLCFWH100BX-BN	PVC Lift & Turn Half Kit Brushed Nickel
MLCFWH100BX-CAFÉ	PVC Lift & Turn Half Kit Café
MLCFWH100BX-ORB	PVC Lift & Turn Half Kit Oil Rubbed Bronze
MLCFWH100-CP	PVC Lift & Turn Half Kit Chrome
MLCFBH100BX-BLM	ABS Lift & Turn Half Kit Black Matte
MLCFBH100BX-BB	ABS Lift & Turn Half KitBrushed Bronze
MLCFBH100BX-BN	ABS Lift & Turn Half Kit Brushed Nickel
MLCFBH100BX-CAFÉ	ABS Lift & Turn Half Kit Café
MLCFBH100BX-0RB	ABS Lift & Turn Half Kit Oil Rubbed Bronze
MLCFBH100-CP	ABS Lift & Turn Half Kit Chrome



## **TOE TOUCH HALF KIT**

PART NO.	DESCRIPTION
MLCFWH200-BN	PVC Toe Touch Half Kit Brushed Nickel
MLCFWH200BX-CAFÉ	PVC Toe Touch Half Kit Café
MLCFWH200BX-ORB	PVC Toe Touch Half Kit Oil Rubbed Bronze
MLCFWH200-CP	PVC Toe Touch Half Kit Chrome
MLCFBH200BX-BN	ABS Toe Touch Half Kit Brushed Nickel
MLCFBH200BX-CAFÉ	ABS Toe Touch Half Kit Café
MLCFBH200BX-ORB	ABS Toe Touch Half Kit Oil Rubbed Bronze
MLCFBH200-CP	ABS Toe Touch Half Kit Chrome

# **FULL KITS**



## **PUSH & SEAL FULL KIT**

PART NO.	DESCRIPTION
MLCFWF300BX-BN	PVC Push & Seal Full Kit Brushed Nickel
MLCFWF300BX-CAFE	PVC Push & Seal Full Kit Café
MLCFWF300BX-ORB	PVC Push & Seal Full Kit Oil Rubbed Bronze
MLCFWF300-CP	PVC Push & Seal Full Kit Chrome
MLCFBF300BX-BN	ABS Push & Seal Full Kit Brushed Nickel
MLCFBF300BX-CAFE	ABS Push & Seal Full Kit Café
MLCFBF300BX-ORB	ABS Push & Seal Full Kit Oil Rubbed Bronze
MLCFBF300-CP	ABS Push & Seal Full Kit Chrome



# **TOE TOUCH FULL KIT**

PART NO.	DESCRIPTION
MLCFWF200BX-BN	PVC Toe Touch Full Kit Brushed Nickel
MLCFWF200BX-CAFÉ	PVC Toe Touch Full Kit Café
MLCFWF200BX-0RB	PVC Toe Touch Full Kit Oil Rubbed Bronze
MLCFWF200-CP	PVC Toe Touch Full Kit Chrome
MLCFBF200BX-BN	ABS Toe Touch Full Kit Brushed Nickel
MLCFBF200BX-CAFÉ	ABS Toe Touch Full Kit Café
MLCFBF200BX-ORB	ABS Toe Touch Full Kit Oil Rubbed Bronze
MLCFBF200-CP	ABS Toe Touch Full Kit Chrome



# LIFT & TURN FULL KIT

PART NO.	DESCRIPTION
MLCFWF100BX-BLM	PVC Lift & Turn Full Kit Black Matte
MLCFWF100BX-BB	PVC Lift & Turn Full Kit Brushed Bronze
MLCFWF100BX-BN	PVC Lift & Turn Full Kit Brushed Nickel
MLCFWF100BX-CAFÉ	PVC Lift & Turn Full Kit Café
MLCFWF100BX-0RB	PVC Lift & Turn Full Kit Oil Rubbed Bronze
MLCFWF100-CP	PVC Lift & Turn Full Kit Chrome
MLCFBF100BX-BLM	ABS Lift & Turn Full Kit Black Matte
MLCFBF100BX-BB	ABS Lift & Turn Full Kit Brushed Bronze
MLCFBF100BX-BN	ABS Lift & Turn Full Kit Brushed Nickel
MLCFBF100BX-CAFÉ	ABS Lift & Turn Full Kit Café
MLCFBF100BX-ORB	ABS Lift & Turn Full Kit Oil Rubbed Bronze
MLCFBF100-CP	ABS Lift & Turn Full Kit Chrome bagged

# **ROUGH-INS & TRIM KITS**





# HALF KIT ROUGH-IN

PART NO.	DESCRIPTION	
MLCFWRK100-CP	PVC Rough-in Half Kit	
MLCFBRK100-CP	ABS Rough-in Half Kit	

## **LIFT & TURN TRIM KIT**

PART NO.	DESCRIPTION
MLCF100-BLM	Lift & Turn Trim Kit Black Matte
MLCF100-BB	Lift & Turn Trim Kit Brushed Bronze
MLCF100-BN	Lift & Turn Trim Kit Brushed Nickel
MLCF100-CAFÉ	Lift & Turn Trim Kit Café
MLCF100-ORB	Lift & Turn Trim Kit Oil Rubbed Bronze
MLCF100-CP	Lift &Turn Trim Kit Chrome
MLCF101-CP	Lift &Turn Trim Kit Chrome - cartride & faceplate only



# **TOE TOUCH TRIM KIT**

PART NO.	DESCRIPTION
MLCF200-BN	Toe Touch Trim Kit Brushed Nickel
MLCF200-CAFÉ	Toe Touch Trim Kit Café
MLCF200-ORB	Toe Touch Trim Kit Oil Rubbed Bronze
MLCF200-CP	Toe Touch Trim Kit Chrome
MLCF201-CP	Toe Touch Trim Kit Chrome - cartridge & faceplate only

# **PUSH & SEAL TRIM KIT**

PART NO.	DESCRIPTION
MLCF300-BN	Push & Seal Trim Kit Brushed Nickel
MLCF300 CAFÉ	Push & Seal Trim Kit Café
MLCF300-ORB	Push & Seal Trim Kit Oil Rubbed Bronze
MLCF300-CP	Push & Seal Trim Kit Chrome
MLCF301-CP	Push & Seal Trim Kit Chrome - cartridge & faceplate only

# **RE-FIT TRIM KITS**



## LIFT & TRIM RE-FIT TRIM KIT

PART NO.	DESCRIPTION
MLCF712BX-BLM	Re-Fit Black Matte Trim Kit Lift & Turn 3/8"
MLCF712BX-BB	Re-Fit Brushed Bronze Trim Kit Lift & Turn 3/8"
MLCF712BX-BN	Re-Fit Brushed Nickel Trim Kit Lift & Turn 3/8″
MLCF712BX-CAFÉ	Re-Fit Café Trim Kit Lift & Turn 3/8″
MLCF712BX-CP	Re-Fit Chrome Trim Kit Lift & Turn 3/8″
MLCF712BX-ORB	Re-Fit Oil Rubbed Bronze Trim Kit Lift & Turn 3/8"
MLCF712BX-PN	Re-Fit Polished Nickel Trim Kit Lift & Turn 3/8"

# **ASSEMBLY INSTRUCTIONS**

### **CLICK-FIT® BATHWASTE INSTALLATION**

Follow the installation instructions outlinedbelow to install Click-Fit® bathwaste.











### STEP 1

Install the thick washer over the threads of the Click-Fit  $\ensuremath{^{\textcircled{\$}}}$  overflow head.

### **STEP 2**

Screw the lock nut on the threads of the Click-Fit<sup>®</sup> overflow head to secure to the tub face.

### **STEP 3**

When pressure testing the system, screw on the red test cap to seal the Click-Fit<sup>®</sup> overflow head.

## **STEP 4**

Remove the red test cap and insert the Click-Fit<sup>®</sup> faceplate into the overflow head with the slots and turn until it locks into position.

### **STEP 5**

Once Click-Fit<sup>®</sup> faceplate is in position, push forward until the faceplate is touching the tub face.



Follow us on Facebook, Google+ and Twitter. www.MainlineCollection.com



